

Technical data sheet

Article number:
924-00560

1UT

Product Group	Crimp Link Terminals
Product Family	Single Grip Pre-Insulated
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Red (RD)
Application Range	Low Voltage
Conductor Size Range mm²	0.5-1.5 mm ²
Diameter (D)	5.8 mm
Length (L)	24 mm
Length (L2)	15 mm
Length (L3)	9 mm
Max Current	19 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
Ø (D2)	4.3 mm
ROHS compliant	Yes

