

## FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **0.66 in Inside and Outside Diameter:** Ensures compatibility with a wide range of shafts and housings.
- **0.09 in Thickness:** Offers a compact design suitable for tight spaces.
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Supports dynamic applications with ease.
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Handles high static loads effectively.

## RS PRO Sintered Bronze Thrust Washer, 0.66 in Diameter

RS Stock No: 528-213



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO sintered bronze thrust washer is designed to provide reliable performance in applications requiring low friction and high wear resistance. Ideal for use in mechanical assemblies, this thrust washer offers excellent load-bearing capabilities, ensuring smooth operation and longevity.

## General Specifications

Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Thrust Washer
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Washer

## Mechanical Specifications

Inside Diameter	0.66 in
Material	Sintered Bronze
Outside Diameter	0.66 in
Thickness	0.09 in

## Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

