

# Throttle plate VABF-B14-F1B1P1-FF14

Part number: 8098885



 [General operating condition](#)

## Data sheet

| Feature                        | Value                                     |
|--------------------------------|-------------------------------------------|
| Mounting position              | optional                                  |
| Operating pressure             | 1.5 bar ... 10 bar                        |
| Operating medium               | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress             |
| LABS (PWIS) conformity         | VDMA24364 zone III                        |
| Storage temperature            | -20 °C ... 60 °C                          |
| Media temperature              | -20 °C ... 60 °C                          |
| Ambient temperature            | -20 °C ... 60 °C                          |
| Product weight                 | 215.5 g                                   |
| Type of mounting               | With through-hole                         |
| Pneumatic connection, port 2   | Flange 1/4 with NAMUR port pattern        |
| Pneumatic connection, port 4   | Flange 1/4 with NAMUR port pattern        |
| Note on materials              | RoHS-compliant                            |
| Material regulator housing     | Wrought aluminium alloy                   |