

Model No. 482

Rotating Gate Valve Lockout, 4in-6-1/2in (10.2cm-16.5cm) Diameter Handles

Best Used For:

LOCKOUT/ TAGOUT Lockout Tagout

 Valve Lockout

Overview & Features

Product Features

- Rotating Gate Valve Lockout Device
- Outward/inward rotation allows for easier installation and storage
- Surrounds the valve operating handle to protect against accidental valve opening
- Unique patented rotating design allow for easier installation in confined space applications
- Each size rotates into itself and nests into the next larger size to save space in safety tool boxes
- Center knockout can be removed for rising stem gate valves
- Multiple workers can apply their personal safety padlocks
- Complete with high visibility permanent safety labels (English, French and Spanish) that can be written-on to identify the responsible person
- Tough, lightweight, dielectric thermoplastic bodies withstand chemicals
- Fits 4in (102mm) to 6-1/2in (165mm) diameter valve handles

Certifications

-
-

Product Details

The Master Lock No. 482 Rotating Gate Valve Lockout Device features a 1-7/8in (48mm) depth and 2-1/2in (64mm) stem opening for 4in (102mm) to 6.5in (165mm) diameter valve handles to surround the valve operating handle to protect against accidental valve opening. The unique, patented rotating design allows for easier installation in confined space applications. Tough, lightweight, dielectric Zenez™ Thermoplastic body withstands chemicals and performs effectively in extreme conditions. Includes high-visibility permanent safety labels.

Product Specifications

Product Number	482
Colour	Red
Description	Commercial Bagged
Master Carton Qty	6

Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu