




LED FIL A60 E27 DIM 4.5W (40W) 470lm 827 Opal

Article number: 146705

BAI LED Filament Dimmable GLS A60 E27 4.5W 2700K Opal 470lm (40W) 230V-240V 360° 60x108mm LED-lamp

LED filament lamps can be seen as the modern sustainable version of the old incandescent lamp. The so-called filaments replace the traditional filament, making the lamps many times more energy-efficient and last much longer. This series of lamps are dimmable (depending on the type of dimmer and the number of lamps to be dimmed on 1 dimmer).



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	LED FIL A60 E27 DIM 4.5W (40W) 470lm 827 Opal
Brand	Bailey
Productseries	LED Filament GLS
Producttype	A60 Opal

ETIM specifications

Socket	E27
Luminous flux [lm]	470 - 470
Nominal voltage [V]	220 - 240
Lamp power [W]	4.5 - 4.5
Colour temperature [K]	2700 - 2700
Diameter [mm]	60
Length [mm]	108
Dimmable	Yes
Lamp shape	Pear-shape
Beam angle [°]	320 - 320
Colour	White
Type of glass/cover	Opal
Lamp designation	A-type
Colour rendering index CRI	80-89
Voltage type	AC
Filament lamp	Yes
Rated luminous flux according to IEC 62612 [lm]	470
Power factor	0.8
Nominal current [mA]	23 - 23
Colour of light according to EN 12464-1	Warm white < 3300 K
Housing colour	White
Average nominal lifetime [h]	15000
Degree of protection (IP)	IP20
Colour consistency (McAdam ellipse)	SDCM6
Min. number of switching cycles	15000
Weighted energy consumption in 1000 hours [kWh]	5
Remote operation possible	No
With movement sensor	No
With remote control	No
Photobiological safety according to EN 62471	RG0
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Suitable for electronic ballast	No
Suitable for magnetic ballast	No
Dimming phase cut-off (trailing edge)	Yes
Dimming phase cut-on (leading edge)	Yes
Dimming Touch and Dim	No
Dimming Zigbee	No
Dimming Bluetooth	No

Dimming Wi-Fi	No
Energy efficiency class according to EU regulation 2019/2015	F
With twilight switch	No
Material of light bulb	Glass

Complementary articles



139704

Lampholder Porcelain E27 White



140398

Lampholder Alu E27 White