

Product data sheet

Specifications

Repacked, GT bend, Mureva Tube
GT, diameter 20mm, IP40, grey



IMT53320W



This repacked option saves 4.976 over the standard condition

Main

range of product	Mureva
Product or component type	Bend
Function available	GT-function
Mounting location	Indoor Outdoor
Nominal cross section	224 mm ²
Diameter	External: 20 mm Internal: 16.9 mm
Colour tint	Grey (RAL 7035)

Complementary

Quantity per set	50 pieces
Ambient air temperature for operation	-5...60 °C
Material	PVC (polyvinyl chloride)
Standards	IEC 61386

Environment

IP degree of protection	IP40
IK degree of protection	IK07
Environmental characteristic	Non-flame propagating
Product certifications	NF

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.6 cm
Package 1 Width	19 cm
Package 1 Length	20 cm
Package 1 Weight	31 g

Contractual warranty

Warranty (in months)	18
----------------------	----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

5 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

90215406-b6bf-44f8-b463-8540d32a6f6b

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No