



**Datasheet** 

## EN

## RS Pro RS-625 Hardened Industrial 5 Port PoE+ 10/100 Ethernet Switch

Stock Number: 2263246




## **Specifications:**

- Power Consumption: 4 Watts Max: 220 mAmps@+5VDC/36mAmps@+30VDC
- PoE Power Budget: 90W @ 70°C
- Power Supply input: Unregulated +44V to +57Volts DC, reverse polarity protection
- Operating Temperature: -40°C to +70°C/-40°F to +158°F
- Ethernet Ports: 5 x RJ45 jack, 10/100Mhz autosensing, crossover auto sensing (Auto MDIX)
- Ports 1-4 IEEE 802.3 af/at compliant: deliver up to 30W to each port
- Unmanaged 10/100Mbps Ethernet
- Housing: IP-30 rated non-conducting polyamide case with Easy Wire Removable screw terminal block
- Weight: 0.235 kg / 8.3 oz.
- Packaged Dimensions: 160x135x49 mm / 6.3x5.3x1.9 ln.

## **Features:**

- 5 Port PoE+ 10/100 Mbs Ethernet Switch
- Redundant dual power inputs: +44V to +57Volts DC
- Compact design with integral DIN mount
- No software required Simply plug in and connect
- Industrial temperature range



Ethernet Ports Yellow: PoE Black: Non-PoE