

Features

- 4 pieces tools set:
- 1 Wire Stripper, stripping range 0.25-0.81mm.
- 1 Side Cutters, max cutting capacity 1.3mm.
- 1 Side Cutters, max cutting capacity 1mm.
- 1 Flat Nose Pliers, 140mm overall, straight tip, 17mm jaw.
- In durable nylon wallet roll.
- Ergonomic anti-slip bi-component handle for a safe, light and comfortable grip.
- Anti-reflection phosphating surface treatment.
- Anti-reflection phosphating surface treatment.
- Laser marking.
- Made in Italy.
- Weight: 407 g.
- Dimension: 210x320mm.

RS PRO Cutters Set, 2 Flush Cutters, 1 Wire-Stripper & Plier, 1 Short Flat-Nose Plier

RS Stock No.: 0715756



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Cutters Set (4pcs)

A professional and hardwearing cutter set come with 2 of Flush Cutters, 1 of Wire Stripper/Plier, and 1 of Short Flat-Nose Plier.

Features and Benefits

- Made in Italy with carbon steel and undergo a controlled atmosphere heat treatment.
- The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.
- The tools are joined with grounded holes and surfaces, thereby allowing precise movements.
- The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours.
- This tools set is ideal for different applications in microelectronics, jewellery making, laboratory, watch making and repairs, DIY.
- Supplied in durable nylon wallet roll.

General Specifications

Cutter Type	2 x Flush Cutters, 1 x Wire Stripper/Plier, 1 x Short Flat-Nose Plier
ESD	No
Number of Tools	4

Mechanical Specifications

Cutter Type	Wire stripper
Stripping holes	Ø 0.25-0.81mm (30-20 awg)
No. of the stripping holes	6
No Sparking	No
Overall Length	165 +/- 2mm
VDE/1000V Approved	No
Height Safe	No
ESD Safe	No
Material	High Carbon Steel
Cutter Type	Flush Side Cutter
Materials Cut	Ø 1.3mm (16 awg) copper wire
No Sparking	No
Overall Length	138mm +/- 2mm
VDE/1000V Approved	No
Height Safe	No
ESD Safe	No
Material	High Carbon Steel
Maximum Cutting Capacity	1.30mm
Cut Type	Flush
Cutter Type	Flush Side Cutter.
Materials Cut	Ø 1.02mm (18 awg) copper wire
No Sparking	No
Overall Length	132mm +/- 2mm
VDE/1000V Approved	No
Height Safe	No
ESD Safe	No
Material	High Carbon Steel
Maximum Cutting Capacity	1.02mm
Cut Type	Flush
Cutter Type	Short flat-nose plier
Hardness	Hrc 48-50
No Sparking	No
Overall Length	146mm +/- 2mm
VDE/1000V Approved	No
Height Safe	No
ESD Safe	No
Material	High Carbon Steel
Steel thickness	3mm
Tip	Flat

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Sizes	Material	Length
238-0722	RS PRO	Wire Stripper	Ø 0.25-0.81mm (30-20 awg) for Stripping Holes	High Carbon Steel	165 +/- 2mm
606-490	RS PRO	Flush Side Cutter	Ø 1.3mm (16 awg) copper wire	High Carbon Steel	138mm +/- 2mm
606-484	RS PRO	Flush Side Cutter	Ø 1.02mm (18 awg) copper wire	High Carbon Steel	132mm +/- 2mm
606-535	RS PRO	Flat Nose Pliers	146mm +/- 2mm	High Carbon Steel	146mm +/- 2mm
xxx-xxxx K4-1	RS PRO	Cutters Set (Flush Cutters, Wire tripper & FN Pliers)	All above	High Carbon Steel	All above

Kit Contains

Name	QTY
Wire Stripper, stripping range 0.25-0.81mm	1
Flush Side Cutters, max cutting capacity 1.3mm	1
Flush Side Cutters, max cutting capacity 1mm	1
Flat Nose Pliers, 140mm overall, straight tip, 17mm jaw	1

