



Werkstatt-Stableuchte SHL 11 S IP 44

Werkstatt-Stableuchte 11 W mit Schalter. Spritzwassergeschützt, IP 44.

- Bestens geeignet in der Werkstatt, bei Hobbyarbeiten usw.
- Inklusive Kompakt-Leuchtstofflampe.
- Leuchtmittel problemlos austauschbar.
- Stabiler, drehbarer Metallhaken.
- Robuster, ergonomisch geformter Griff mit 6-Kant-Wulst gegen Wegrollen.
- Schlag- und bruchfestes Schutzrohr mit Blendschutz.
- Mit elektronischem Vorschaltgerät für flackerfreies Licht und geringe Erwärmung.
- Wirkungsgrad Vorschaltgerät: A2 BAT
- Länge ca.: 47 cm

Inspection Lamp For Garage SHL 11 S IP 44

Inspection lamp for garage 11W with switch. Splash-water proved, IP 44.

- Ideal for workshops, when working on your hobby etc.
- Includes compact fluorescent lamp.
- Lamp can be replaced without any problem.
- Robust, rotatable metal hook.
- Robust, ergonomically formed handle with 6 ribs to stop it against rolling away.
- Impact and break-proof protective tube with glare protection.
- With electronic ballast for flicker-free light and low heat generation.
- Ballast efficiency: A2 BAT
- Length appr.: 47 cm



Artikel-Nr. Article No.	Barcode 4007123...	VPE UP	Kabellänge Cable length	Kabelbezeichnung Cable	Leistung Output	Lichtstrom Luminous flux	Wirkungsgrad Lampe Lamp efficacy	Farbtemperatur Colour temperature	Fassung Fittings
1 17728 0	610389	2	5 m	H05RN-F 2x1,0	11 W	898 lm	82 lm/W	4000 K	G23

Lieferbar ab Juni 2013. / Available as from June 2013.

Empfohlenes Zubehör: / Recommended accessories:

Artikel-Nr. Article No.	Barcode 4007123...	VPE UP	Bezeichnung Description	Leistung Output	Lichtstrom Luminous flux	Wirkungsgrad Lampe Lamp efficacy	Farbtemperatur Colour temperature	Farbwiedergabeindex Colour rendering index	Fassung Fittings
1 17728 0 001	617692	1	Leuchtstofflampe Fluorescent lamp	11 W	898 lm	82 lm/W	4000 K	82	G23