

FEATURES

- Black RJ11 (6 way)
- 2 Ports Socket to Socket
- UTP Unshielded coupler
- PBT Material for Durable design
- Phosphor bronze contacts with gold over nickel plating
- Dimensions: 20.55 x 14.48 x 26.98 mm

RS PRO RJ11 Coupler, 2 Port, Unshielded

RS Stock No.: 186-3133



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO, this RJ11 Modular Coupler enables RJ11 connector plugs and cable assemblies to be patched together straight through a patch panel or blank faceplates. This unshielded modular inline coupler has a durable design and can easily press-fit into pre-cut panels. This is ideal for those who need a custom network architecture solution.

General Specifications

Type	Coupler
Interface Type	RJ11
Number of Ports	2
Shield Type	Unshielded
Wiring Configuration	Straight Through
Colour	Black
Contact plating	Gold plating over nickel
Housing Material	Engineering thermoplastic flammability rating UL 94V-0
Contact Material	0.35 mm thickness phosphor bronze
Application	RJ11 connectors is often used with landline telephones and older modem connections. As such, this modular connector can be used to organize communication network architecture or simply serve as a cable extension solution.

Mechanical Specifications

Length	20.55mm
Width	14.48mm
Depth	26.96mm

Approvals

Compliance/Certifications	UL 94V-0/2011/65/EU and 2015/863
----------------------------------	----------------------------------

