


RASE30-XL-N-FA125

Plummer block housing unit

Plummer block housing units RASE...-FA125, cast iron housing, radial insert ball bearing with eccentric locking collar, R seals, with anti-corrosion protection

X-life

Technical information



Your current product variant

Material	GG	Grey cast iron
Groove	N	Cast iron housing with undercut slot for end caps
Manufacturing instruction	FA125	Unit with Corrotect coating, corrosion-resistant

Main Dimensions & Performance Data

d	30 mm	Bore diameter
L	158 mm	Length total
H ₂	82 mm	Height
≈m	1.184 kg	Weight

Mounting dimensions

J	117.5 mm	Distance fixing bore
N	14 mm	Width (slot)
N ₁	22 mm	Length (slot)



Dimensions

H	42.9 mm	Distance shaft axis
A	40 mm	Width (base)
A ₁	25 mm	Width (head)
H ₁	17 mm	Heigth (base)
B ₁	48.5 mm	Locking collar total width
S ₁	30.2 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication

Additional information

ASE06-FA125	Housing
GE30-XL-KRR-B-FA125	Bearing designation
KASK06	Protecting cap

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.