



English

Product Datasheet

Stock No: 146-9092

RS PRO DC Voltage Datalogger

EN



Features

- Memory for 32000 readings
- The data can be drafted to graphic curve through PC software
- Selectable sampling time: 400Hz(2.5ms),0.0025s, 2s, 5s, 10s, 30s, 1m, 5m, 10m, 30m, 1hr, 2hr, 3hr, 6hr, 12hr, 24hr
- Triple LED light (Red, Yellow, and Green) to indicate running state
- The collected data can be downloaded to PC software via USB interface
- Low and high alarm value can be settable by users.
- Two Modes (Auto and Manual) used for activating datalogging
- Measurement Accuracy (Full scale): $\pm 0.5\%$
- Measurement range: 0-30V
- Low Battery Indication
- Operating Temperature: 32 to 122°F (0 to 50°C)
- Storage Temp.: -4 to 140°F (-20 to 60°C)
- Operating Humidity: < 80% RH
- Storage Humidity: < 80%RH
- Weight 20g
- Size 130x30x25mm