

FEATURES

- Three poles
- Three-phase starter
- Automatic motor starter functionality
- Disconnect switch not included
- DOL starter
- Range available with and without isolator
- Power rating of 5.5kW
- Voltage rating of 230VAC
- Current rating of 9 to 14A

RS PRO 5.5 kW DOL Starter, 230 V ac, 3 Phase, IP65

RS Stock No.: 725-5503



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

This handy 5.5 kW automatic 3-phase starter can be used to reduce the current required when starting up induction motors. These types of starters are best-suited for use with induction motors rated below 5 hp.

General Specifications

Motor Starter Type	DOL
Motor Starter Functionality	Automatic
Number of Poles	3P
Motor Supporting Range	5.5kW to 11kW
Reversibility	No
Enclosure	Yes
Material	Plastic
Additional Features	Disconnect Switch Not Included
Applications	Large fans and water pumps to workshop machinery

Electrical Specifications

Phase	3
Power Rating	5.5kW
Voltage Rating	230VAC
Current Rating	9A to 14A
Maximum Allowed Motor Current	14A



Mechanical Specifications

Overall Length	193mm
Overall Width	88mm
Overall Depth	134mm

Operation Environment Specifications

25°C to 60°C
2

Protection Category

IP Rating	IP65

Approvals

Compliance/Certifications	CE
Standards Met	IEC/EN 60947-1, IEC/EN 60947-4-1, RoHS Compliant



