

Microflex® 93-852

CHEMICAL & LIQUID PROTECTION



STYLE #	COATING MATERIAL	GRIP DESIGN	CUFF STYLE	COLOUR	EN SIZE	LENGTH MM	THICKNESS MM	PACKAGING
93-852	Nitrile	Textured Surface	Beaded	Black	5.5 - 6, 6.5 - 7, 7.5 - 8, 8.5 - 9, 9.5 - 10	245	0.12	100 gloves per dispenser, 10 dispensers per shipper carton, 1000 gloves per shipper carton

DESCRIPTION

- Distinctive black colour hides stains and provides a contrasting backdrop for identifying lighter coloured material.
- Offers a higher tensile strength compared to both ASTM D6319 and EN 455 standards, allowing the hands to move freely and comfortably while wearing the Microflex 93-852.
- Fully textured design and non-foaming formula enable wearers to have a firm wet grip when handling objects.
- Contains no natural rubber latex and powder-free, to help protect wearers from Type I skin allergies, skin irritation and dryness.

REMARKS

- Antistatic according to EN1149



Distinct colour to mask stains for special applications

PRIMARY INDUSTRIES



IDEAL APPLICATIONS

- Analytical testing/Measurements
- Biotechnologies
- Filtration processes
- Food Processing
- Laboratory analysis
- Laboratory testing
- Light assembly tasks
- Light assembly of oil-coated pieces
- Light duty maintenance and clean up
- Mechanical jobs
- Paint and spray shops
- Pharmaceutical manufacturing
- Protection from blood and other bodily fluids



CATEGORY III



Print date: 16-07-2016

Ansell Healthcare Europe N.V. (European Head Office)

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

<http://www.ansell.eu> • E-mail info@ansell.eu

