



Main

Range	Acti9
Product or component type	Dual source incomer
Device application	Distribution
Provided equipment	Extension box
Colour tint	White
Colour code	RAL 9001

Complementary

[Ie] rated operational current	125 A at 415 V AC
Poles description	4P
Mounting mode	Surface mounting
Enclosure material	Steel
Height	270 Mm
Width	475 Mm
Depth	140 Mm
Internal depth	102 Mm

Environment

IP degree of protection	IP3x
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.0 Cm
Package 1 Width	34.0 Cm
Package 1 Length	49.0 Cm
Package 1 Weight	7.765 Kg

Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : Commercialised
