



## RS PRO Miniature Micro Switch

RS Stock No.: 241-234

### Features

- SINGLE POLE CHANGEOVER
- FINE SILVER CONTACTS
- SNAP ACTION MECHANISM
- SILVER /GOLD PLATED TERMINALS
- ALSO AVAILBLE WITH LOW ACTUATING FORCE
- CONFORM TO IEC 1508-1 STANDARD.
- **CE** APPROVED.



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

- *Single pole change over.*
- *Snap action mechanism.*
- *Fine silver contacts.*
- *Long mechanical & electrical life.*
- *Silver / Gold plated terminals.*
- *Also available with low actuating force.*
- *Confirm to IEC 1058-1 Standard.*

## General Specifications

Contact Configuration	SPDT
Contact Arrangement	1No + 1NC,snap action.
Contacts	Fine silver contacts.
Terminals	Copper alloy, silver plated.
Plunger	Thermoplastic.
Case	Glass filled flame retardant thermoplastic(UL94-V0).

## Electrical Specifications

Electrical Rating		
	Load	Rating
	AC(Resistive)	5 A at 250V.
	DC(Resistive)	0.5 A at 125V or 0.25 A at 250V.
	DC(Inductive)	0.06 A at 125V or 0.03 A at 250V.
Contact Resistance		10 milliohms(max.).
Insulation Resistance		1000 Megaohms(min.).
Dielectric Strength		1 KV AC for one minute.
Electrical life		50,000 Operations.
Mechanical life		100000 Operations.

## Mechanical Specifications

Actuating Force (AF)	20 gms. (max).
Release Force(RF)	7 gms. (min.).
Free Position(FP)	19.4 mm. (max.).
Operating Position(OP)	10.4 mm.
Pretravel	9.0 mm.(max).
Overtravel	4.0
Movement Differential(MD)	2.6 mm.(max),
Mounting	Switches should be mounted on a flat surface using two M2 or #2 unified thread screws.
Unit Weight	2.3 gms. Approx.
Salient Feature	Plain stimulated lever, 2 mm quick-connect tabs.

## Operation Environment Specifications

Operating Temperature Range	-25°C to +85°C.
-----------------------------	-----------------

## Protection Category

IP Rating	IP40(enclosure).
-----------	------------------

## Approvals

Compliance/Certifications	CE
---------------------------	----

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories