

Features

- Secured with self-tapping screws (N°6)
- Releasable locking feature

RS PRO PCB Spacers

RS Stock No.: See table



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Female support posts provide secure fixings for printed circuit boards
- Releasable locking retainer holds board firmly but is easily released
- Can be secured using a N°6 or 3.5mm self-tapping screw (supplied separately)

Material Specifications

Material Type	Nylon 66
Type	Snap-In Spacer
Colour	Natural
Flammability Rating	UL94-V2
Working Temperature Range	-40°C to +85°C

Part Specifications

Parameters	0304268	0304269	0304271	0304272	0304274	0304275	0304277	0304278	0304279	0304280
Body Height (A)	6.4mm	9.5mm	12.7mm	15.9mm	19.1mm	22.2mm	25.4mm	28.6mm	31.7mm	35.7mm
PCB Hole Dia	4.0mm	4.0mm	4.0mm	4.0mm	4.0mm	4.0mm	4.0mm	4.0mm	4.0mm	4.0mm
PCB Thickness	1.57mm	1.57mm	1.57mm	1.57mm	1.57mm	1.57mm	1.57mm	1.57mm	1.57mm	1.57mm
Self-Tapping Screw Size	N°6 (3.5mm)	N°6 (3.5mm)	N°6 (3.5mm)	N°6 (3.5mm)	N°6 (3.5mm)	N°6 (3.5mm)	N°6 (3.5mm)	N°6 (3.5mm)	N°6 (3.5mm)	N°6 (3.5mm)
Hole Depth (B)	5.2mm	7.9mm	7.9mm	7.9mm	7.9mm	7.9mm	7.9mm	7.9mm	7.9mm	7.9mm

