

CES-STPG-GY-4X5 - Cable sleeve



1410136

<https://www.phoenixcontact.com/gb/products/1410136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable sleeve, small, no. of conductors: 4, type: Round cable, slotted, external cable diameter: 4x 4.4 mm ... 4.7 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

Product description

Slotted cable sleeve

Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 1410136 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AF7CCX |
| Product key | AF7CCX |
| Catalog page | Page 681 (C-2-2019) |
| GTIN | 4046356776288 |
| Weight per piece (including packing) | 7.06 g |
| Weight per piece (excluding packing) | 7.06 g |
| Customs tariff number | 40169997 |
| Country of origin | PL |

CES-STPG-GY-4X5 - Cable sleeve

1410136

<https://www.phoenixcontact.com/gb/products/1410136>




Technical data

Product properties

| | |
|-------------------|--------------|
| Product type | Cable sleeve |
| No. of conductors | 4 |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 19.5 mm |
| Height | 17 mm |
| Length | 29.5 mm |

Material specifications

| | |
|--|---------------------|
| Material | SEBS (halogen-free) |
| Flammability rating according to UL 94 | V0 |

Cable/line

| | |
|-------------------------|----------------------|
| External cable diameter | 4x 4.4 mm ... 4.7 mm |
|-------------------------|----------------------|

Characteristics

| | |
|--------------------|-------------|
| Seal size | small |
| Design, Format | Round cable |
| Design, Cable seal | slotted |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|---------------------------|
| Degree of protection | IP54 |
| Ambient temperature (operation) | -40 °C ... 80 °C (static) |

CES-STPG-GY-4X5 - Cable sleeve


1410136

<https://www.phoenixcontact.com/gb/products/1410136>



Drawings

Dimensional drawing



Dimensional drawing

CES-STPG-GY-4X5 - Cable sleeve



1410136

<https://www.phoenixcontact.com/gb/products/1410136>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1410136>



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026

DNV

Approval ID: TAE00003VJ

CES-STPG-GY-4X5 - Cable sleeve



1410136

<https://www.phoenixcontact.com/gb/products/1410136>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27144425 |
|-------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000451 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CES-STPG-GY-4X5 - Cable sleeve



1410136
<https://www.phoenixcontact.com/gb/products/1410136>

Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
| EF3.0 Climate Change | |
| CO2e kg | 0.073 kg CO2e |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk