



tesa[®] 4323

Product Information



General purpose paper masking tape

Product Description

tesa[®] 4323 is a finely creped paper masking tape with a natural rubber adhesive.

Sustainable Aspects

57% bio-based content in total product excluding liner (by weight)



For more information: <https://www.tesa.com/product-sustainability>

Product Features

- The crepe paper backing ensures a good conformability.
- The natural rubber adhesive system features good adhesion to multiple surfaces as well as a good tack.
- The masking tape offers excellent paint anchorage, making it suitable for light duty spray painting.

Application Fields

The product is suitable for general purpose applications: masking, holding, sealing, fixing, light duty packaging etc.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|-----------------------|--|--------|
| • Backing material | slightly-creped paper | • Total sustainable product excl. liners by weight (acc. EN 16785) | 57 % |
| • Type of adhesive | natural rubber | • Total thickness | 125 µm |

Properties/Performance Values

- | | | | |
|-----------------------|-----------|-----------------------------------|-------|
| • Elongation at break | 10 % | • Temperature resistance (30 min) | 80 °C |
| • Tensile strength | 33 N/cm | • Temperature resistance (60 min) | 60 °C |
| • Hand tearability | very good | | |

Adhesion to Values

- | | |
|---------|----------|
| • steel | 2.8 N/cm |
|---------|----------|

For latest information on this product please visit <http://l.tesa.com/?ip=04323>



tesa[®] 4323

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?ip=04323>