



Multi Purpose



Light Duty

Durable gloves with grip offering high tactility in dry to slightly oily conditions

- **Augmented durability:** Featuring a polyurethane-coated palm, EDGE[®] 48-125 protective gloves offer EN level 4 abrasion protection as well as good grip and tear resistance
- **Maximized comfort:** These light-duty hand protection gloves' seamless knitted liner is combined with elasticized knitwrist dipped into black, white or grey polyurethane coating, which provide good flexibility and dexterity compared to cotton canvas and thick cotton gloves
- **Genuine versatility:** Made from 15-gauge polyester liner, which is highly comfortable and dexterous, EDGE[®] 48-125 safety work gloves are economical and come in black, white and grey



Industries

- Automotive
- Electronics
- Oil and gas
- Machinery and Equipment
- Transportation
- Recycling and Waste Disposal

Applications

- Assembly of small pieces
- General handling
- Packaging
- Quality inspection

Key Features

- **Polyurethane coating:** Abrasion and tear-resistant gloves with grip
- **Seamless structure:** For safety gloves with added comfort and agility
- **15-gauge polyester liner:** For lightweight, tactile and dexterous gloves

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN 388



4131

EN388: 2016



4121A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE [®] 48-125	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Polyester Cuff Style: Knitwrist	15	6, 7, 8, 9, 10, 11	215-270 mm, 8.46-10.63 inches	White	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699