



64974 - OT K11 C130W 240V R7S 117MM GE BX1/10MIC

Specifications

General characteristics:

Wattage [W]	130
Voltage [V]	240
Lumens [lm]	2440
Rated Lumens per Watt (Efficacy) [lm/W]	18.76923
Cap/Base	R7s
Bulb Shape	Tubular
Bulb Diameter [mm]	8.80
Colour temperature [K]	2900
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	1000
Dimming Capability	Yes
Coil type	CC-8
Maximum Overall Length [mm]	119
DUN Code	10043168649749
EAN Code	0043168649742
Net weight per piece [g]	7
Gross weight per piece [g]	20
Pack Quantity	10
Inner pack type	BOX
Outer pack type	OUTER BOX
Layer quantity EUR (PC)	3200
Layer quantity UK (PC)	4000
Pallet quantity EUR (PC)	16000
Pallet quantity UK (PC)	20000
Outer case size	125 x 90 x 38 (mm)
Energy Efficiency Class	D
Brand	General Electric (GE)
Product status	Available