



### Main

Range	Acti 9
Product or component type	Add-on residual current devices
Device short name	Vigi iC60
Poles description	2P
[In] rated current	25 A
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth leakage protection type	Type AC
Network type	AC
Network frequency	50/60 Hz
[Ue] rated operational voltage	230/400 V AC 50/60 Hz conforming to EN 61009-1 230/415 V AC 50/60 Hz conforming to IEC 61009-1
Standards	IEC 61009-1 EN 61009-1
9 mm pitches	3

### Complementary

Device location in system	Outgoer
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2
Range compatibility	Acti 9 iC60 Acti 9 Reflex iC60
Product compatibility	Single terminal
Local signalling	Trip indicator
Mounting mode	Clip-on
Mounting support	DIN rail

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical connection to mcb	Plug in
Comb busbar and distribution block compatibility	Bottom: YES
Height	91 mm
Width	27 mm
Depth	73.5 mm
Net weight	0.165 kg
Connections - terminals	Tunnel type terminal downside for 1 cable(s) 1...25 mm <sup>2</sup> rigid without cable end Tunnel type terminal downside for 1 cable(s) 1...16 mm <sup>2</sup> flexible without cable end Tunnel type terminal downside for 1 cable(s) 1...16 mm <sup>2</sup> flexible with cable end
Wire stripping length	14 mm for bottom connection
Tightening torque	2 N.m bottom

## Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 conforming to IEC 60947-2
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to IEC 61009-1
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	159 g
Package 1 Height	8.5 cm
Package 1 width	8.5 cm
Package 1 Length	12 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------