



art.	mm	L mm	A mm	S mm	g
000530036	36	317	80,0	13,5	573
000530038	38	320	83,5	15,0	740
000530041	41	342	90,0	15,0	922
000530046	46	396	100	16,0	1120
000530050	50	412	102	17,0	1200
000530055	55	457	112	18,0	1300
000530060	60	492	122	18,0	1600
000530065	65	528	132	19,0	1800
000530070	70	572	142	20,0	2200
000530075	75	608	152	21,0	2800
000530080	80	645	162	22,0	2900
000530085	85	690	173	23,0	3900
000530090	90	690	173	23,0	3900
000530095	95	847	195	25,0	5500
000530100	100	847	195	25,0	5500
000530105	105	1000	217	28,0	7700
000530110	110	1000	217	28,0	7700
000530115	115	1000	225	28,0	7000
000530120	120	1000	225	28,0	7300
000530125	125	1000	225	28,0	7300
000530130	130	1000	225	28,0	7600
000530135	135	1000	225	28,0	7400