

KBU 35 QW

Universal magnetic core drill for up to 35 mm

Order number:: 7 270 54 61 00 0



Small and powerful single-speed universal magnetic core drill with clockwise/anti-clockwise operation and maximum functionality for flexible working on the construction site.

- Extremely resilient construction thanks to sturdy machine design with swivel-mounted motor cable protection hose. Designed for tough use in industry and manual trades.
- Perfect power-to-weight ratio thanks to compact, weight-optimised design and FEIN 1100 W high-power motor with high speed stability for reliable and economical working.
- With clockwise/anti-clockwise operation, electronic speed setting and a 260 mm stroke range, this is a universal tool for core drilling, twist drilling, tapping, countersinking and reaming.
- Small and lightweight.
- Simple operating concept avoids mix-ups and can be clearly seen by the user.
- Additional magnetic switch in the drill jig.
- Tool-free core bit quick change system.
- Speed-controlled tacho electronics.
- High magnetic holding force.
- Convenient magnetic holding force display.
- Integrated coolant tank.
- Feed handwheel can be moved from one side to the other.
- Tilt sensor.
- Speed saving "memory function".



KBU 35 QW

Universal magnetic core drill for up to 35 mm

Order number:: 7 270 54 61 00 0

Technical data

Input	1 100 W
Output	550 W
Speed, full load	130 - 520 rpm
Twist drill max. Ø	16 mm
Core drill, drilling depth max.	50 mm
Tapping	M 14
Countersinking max. Ø	31 mm
Reaming max. Ø	16 mm
Carbide core drill bit max. diameter	35 mm
HSS core drill max. Ø	35 mm
Core drill holder	3/4 in Weldon
Changing the core bit	tool-free
Stroke	135 mm
Total stroke range	260 mm
Magnetic holding power	10 000 N
Magnetic foot dimensions	175 x 80 mm
Cable with plug	4 m
Weight according to EPTA	10,6 kg
Corded	X

Included in price::

1 case
1 coolant tank
1 lashing strap
1 swarf hook
1 centering pin
1 contact guard