

FEATURES

- Galvanised alloy steel Shackle with crew pin
- Meets U.S.A. regulations RR-C-271D Type IVA, grade A,
- Pin diameter of 25 mm
- Jaw width of 37 mm

RS PRO Bow Shackle, Alloy Steel, 6.5t

RS Stock No.: 124-4818



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS Pro Shackle Anchor Bow-Screw Pin, made from forged alloy. Fatigue resistant, perfect for a wide variety of lifting applications on dynamic loads. These shackles can take loads from many directions developing minimal side load.

General Specifications

Shackle Type	Bow Shackle
Pin Type	Screw Pin
Safe Working Load	6.5t
Material	Alloy Steel
Finish	6:1
Safety Factor	Hot dip galvanised
Application	Wire Rope Slings, Moderate to heavy lifting loads, Industrial crane rigging on board large ships, Commonly used in personal safety gear including climbing and mountaineering harnesses

Mechanical Specifications

Shackle Diameter	22mm
Jaw Width	37mm
Pin Diameter	25mm

Operation Environment Specifications

Approved for use at	-40°C to 204°C
----------------------------	----------------

Approvals

Standards Met	Meets U.S.A. regulations RR-C-271D Type IVA, grade A, class 2
----------------------	---

