



LASE40-XL-N

Plummer block housing unit

Plummer block housing units LASE, cast iron housing, radial insert ball bearing with eccentric locking collar, L seals

X-life

Technical information



Your current product variant

Material	GG	Grey cast iron
Groove	N	Cast iron housing with undercut slot for end caps

Main Dimensions & Performance Data

d	40 mm	Bore diameter
L	179 mm	Length total
H 2	99 mm	Height
≈m	1.97 kg	Weight

Mounting dimensions

J	138.25 mm	Distance fixing bore
N	14 mm	Width (slot)
N 1	26 mm	Length (slot)



Dimensions

H	49.2 mm	Distance shaft axis
A	48 mm	Width (base)
A ₁	30 mm	Width (head)
H ₁	19 mm	Heigth (base)
B ₁	56.5 mm	Locking collar total width
S ₁	35.1 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication

Additional information

ASE08-FA125	Housing
GE40-XL-KLL-B	Bearing designation
KASK08	Protecting cap

Temperature range

T _{min}	-40 °C	Operating temperature min.
T _{max}	180 °C	Operating temperature max.