

Metal Cutter XGT®

CS002G

40Vmax • 185 mm • 3 500 min⁻¹

Powerful XGT® battery powered Metal Cutter

Cordless Metal Cutter with built-in dust box, electric brake and twin LED-working lights. The maximum cutting capacity with 185 mm wheel/blade is 67 mm.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	3500 min ⁻¹
Max. Cutting Depth at 90°	67 mm
Blade Diameter	185 mm
Bore Size (Arbor Diameter)	30 mm
Electronic brake	✓
Sound Power Level (L _{WA})	113 dB(A)
Sound Pressure Level (L _{pA})	102 dB(A)
Product net weight	2,6 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	4,2 - 5,4 kg
Product Dimensions (L x W x H):	350 x 232 x 270 mm

User benefits

- Soft start for smooth start-ups
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Brushless maintenance-free and long-life motor
- Electric brake for maximum productivity and increased operator safety
- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing