



ENGLISH

Datasheet

Stock No: 299-3948

RS Pro Pneumatic Straight Threaded-to-Tube Adapter, R 1/8 Male, Push In 5 mm



Product Details

Straight Adaptor - Male Tapered/Parallel

Threaded, Tube-to-Tube & Adaptors

Threaded Tube-to-Tube & Adaptors

The push-on and screw collar design of these fittings makes them secure and suitable for instrumentation, vacuum and general purpose applications, and they can be used with nylon or polyurethane tubing.

Operating Temperature Range -18 to +70°C

Operating Pressure of -1 to 15 bar

Specifications:

Threaded Connection	R 1/8 Male
Tube Connection	Push In 5 mm
Tube Connection - Tube Size	5mm
Threaded Connection - Thread Size	1/8in
Threaded Connection - Gender	Male
Manufacturer Series	1000
Threaded Connection - Thread Standard	R
Tube Connection - Type	Push In
Maximum Operating Pressure	15 bar
Minimum Operating Temperature	-18°C
Maximum Operating Temperature	+70°C