

NSYBRF12PLAG

19" fixed chassis 12U for PLA enclosure
H750xW750mm



Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	19" & nbsp; rack
Application	Multi-purpose
For enclosure nominal dimensions	-
Rack type	Fixed
Mounting location	Front of enclosure
Range compatibility	Thalassa PLA Thalassa PHD
Device composition	Fixing elements 2 19" uprights
Quantity per set	Set of 1
Number of units 19"	12

Complementary

Material	Sheet steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Lock type	Lock 5 mm double bar
Fixing mode	By fixing element
Permanent permissible load	3 kg per unit
Height	750 mm nominal:
Thickness	2 mm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.