



### Main

Commercial Status	Commercialised
Range of product	Harmony XVR
Product or component type	Prewired rotating mirror beacon
Sound signalling	Without
Device short name	XVR
Mounting diameter	106 mm
IP degree of protection	IP55 (with accessory) conforming to IEC 60529 IP23 conforming to IEC 60529
[Us] rated supply voltage	24 V AC/DC
Light source	High luminosity LED, orange

### Complementary

Material	PMMA (polymethyl methacrylate) (globe) ABS (acrylonitrile butadiene-styrene) (body part)
CAD overall width	106 mm
CAD overall depth	106 mm
Product weight	0.5 kg
Marking	CE
Product mounting	By 3 M4 screws
Supply voltage limits	21.6...26.4 V AC 19...30 V DC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	125 mA
Flashing frequency	2.3 Hz
Clamping connection capacity	0.83 mm <sup>2</sup>
AWG gauge	18
Cable length	400 mm

### Environment

Standards	EN 61000-6-2 EN 61000-6-4
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Class of protection against electric shock	Class II conforming to IEC 61140


### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0808 - <a href="#">Schneider Electric declaration of conformity</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Rotating Mirror Beacon

Dimensions



Rotating Mirror Beacon

Panel Cut-out

