

CZL10-12BM



COPPER BELL MOUTH LUG 10SQMM M12 ST



Product image
not available

General Information

Extended Product Type	CZL10-12BM
Product ID	7TBH007940R0106
EAN	5415022191745
Catalog Description	COPPER BELL MOUTH LUG 10SQMM M12 ST
Long Description	Australian Standard Series Copper Bell Mouth Lug, Cable 10 Millimeters Squared, Stud Size M12, Tin Plated

Ordering

EAN	5415022191745
Minimum Order Quantity	100 piece
Customs Tariff Number	8536904000

Dimensions

Product Net Weight	4.536 g
--------------------	---------

Container Information

Package Level 1 EAN	30786209802409
Package Level 2 Units	3000 piece
Package Level 2 Width	25.4 mm
Package Level 2 Height	25.4 mm
Package Level 2 Depth / Length	25.4 mm
Package Level 3 Units	3000 piece

Additional Information

Brand / Label	Spec-Kon
Insulation Material	None
Material	Copper
Product Main Type	COMPRESSION CONNECTORS
Product Name	COPPER LUG
Product Type	Metric, Copper One-Hole Standard Barrel - Bell Shaped End
UPC	786209802705

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	CZL10-12BM
Instructions and Manuals	CZL10-12BM

Classifications

ETIM 6	EC001051 - Tube cable lug for copper conductors
UNSPSC	39121405
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors



Product image
not available