



DCD995P2

18V XR Li-Ion Brushless Premium Hammer Drill Driver

Selling Proposition

- Latest generation 18V XR Li-Ion Brushless XRP hammer drill driver featuring NEW XR 5.0Ah Li-Ion battery technology
- Tough 3 speed all metal transmission for increased runtime and longer tool life
- Electronic Clutch with 11 position adjustable torque control for optimised precision when screw driving
- Includes a TStak Compatible Kitbox to organise you tools and accessory storage
- 13 mm ratcheting keyless chuck with automatic spindle lock for fast bit changes
- Efficient intelligent trigger allowing total control over all applications
- Foot LED with delay feature for improved visibility and flashlight functionality
- Improved grip design providing greater application control and maximum comfort
- Li-Ion battery packs allows for superior insertion and removal with state of charge indicator
- Steel belt hook and magnetic bit holder ensure strong storage solutions
- Multi voltage charger for use with 18V, 14.4V and 10.8V XR Li-Ion battery packs
- Part of the intelligent XR Lithium Ion Series designed for efficiency and making applications faster

Standard Equipment

- 2 x 5.0Ah XR Li-Ion battery packs with state of charge indicator
- Multi-voltage XR charger
- Belt hook
- Magnetic bit holder
- Multi position side handle

Warranty Specifications

- 3 Year Limited Warranty
- 30 Day Money Back Guarantee
- 1 Year Free Service Contract

Specifications	
Voltage	18 V
Battery Capacity	5.0 Ah
Chuck Capacity	1.5-13 mm
Power Output	650 Watts
No Load Speed	0-450/1300/2000 rpm
Beats per Minute	0-7650/22100/34000 bpm
Max Torque	80 Nm
Max. Drilling Capacity [Wood]	50 mm