

LONG LIFE SANDING WOOD AND PAINT

PRO

- 1 Tear-resistant X-cloth backing
- 2 Extra strong belt joint for roughest challenges



BOSCH

PRO X440 SANDING BELT

PRO



- For sanding wood and paint, eg when sanding old paint and floor lacquer or finishing hardwood floors
- Highly efficient for painters: Long Life
- Designed for sanding wood and paint



PRODUCT PROPERTIES				ORDERING INFORMATION				
	Belt dimensions, width mm	Belt dimensions, length mm	Grit	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number
	40	305	40	C1e	3	2	188 562	2 608 606 929
	40	305	40	P0b	10	1	699 716	2 608 608 L87
	40	305	60	C1e	3	4	165 426	2 608 606 206
	40	305	60	P0b	10	1	699 723	2 608 608 L88
	40	305	80	C1e	3	4	165 433	2 608 606 207
	40	305	80	P0b	10	1	699 730	2 608 608 L89
	40	305	120	C1e	3	4	165 440	2 608 606 208
	40	305	120	P0b	10	1	699 747	2 608 608 L90
	40	305	180	C1e	3	4	165 457	2 608 606 209
	60	400	40	C1e	3	2	163 361	2 608 606 000
	60	400	40	P0f	10	2	699 754	2 608 608 L91
	60	400	60	C1e	3	4	163 378	2 608 606 001
	60	400	60	P0f	10	4	699 761	2 608 608 L92
	60	400	80	C1e	3	4	163 385	2 608 606 002
	60	400	80	P0f	10	4	699 778	2 608 608 L93
	60	400	100	C1e	3	4	163 392	2 608 606 003
	60	400	100	P0f	10	4	699 785	2 608 608 L94
	60	400	150	C1e	3	4	163 408	2 608 606 004
	60	400	240	C1e	3	4	163 415	2 608 606 005
	65	410	40	C1e	3	2	163 514	2 608 606 015
	65	410	60	C1e	3	4	163 521	2 608 606 016
	65	410	80	C1e	3	4	163 538	2 608 606 017
	65	410	100	C1e	3	4	163 545	2 608 606 018
	65	410	120	C1e	3	4	163 552	2 608 606 019
	65	410	150	C1e	3	4	163 569	2 608 606 020
	65	410	180	C1e	3	4	163 576	2 608 606 021
	65	410	220	C1e	3	4	163 583	2 608 606 022
	75	457	40	C1e	3	2	163 682	2 608 606 032
	75	457	40	P0f	10	2	699 839	2 608 608 L99
	75	457	40	P0f	10	2	711 142	2 608 608 M99
	75	457	60	C1e	3	4	163 699	2 608 606 033
	75	457	60	P0f	10	4	699 846	2 608 608 M00
	75	457	80	C1e	3	4	163 705	2 608 606 034
	75	457	80	P0f	10	4	699 853	2 608 608 M01
	75	457	100	C1e	3	4	163 712	2 608 606 035
	75	457	120	C1e	3	4	163 729	2 608 606 036
	75	457	120	P0f	10	4	699 860	2 608 608 M02



BOSCH

PRO X440 SANDING BELT

PRO

PRODUCT PROPERTIES				ORDERING INFORMATION				
	Belt dimensions, width mm	Belt dimensions, length mm	Grit	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number
	75	457	150	C1e	3	4	163 736	2 608 606 037
	75	457	180	C1e	3	4	163 743	2 608 606 038
	75	457	220	C1e	3	4	163 750	2 608 606 039
	75	480	40	C1e	3	2	163 781	2 608 606 042
	75	480	60	C1e	3	4	163 798	2 608 606 043
	75	480	80	C1e	3	4	163 804	2 608 606 044
	75	480	100	C1e	3	4	163 811	2 608 606 045
	75	480	120	C1e	3	4	163 828	2 608 606 046
	75	480	150	C1e	3	4	163 835	2 608 606 047
	75	480	180	C1e	3	4	163 842	2 608 606 048
	75	480	220	C1e	3	4	163 859	2 608 606 049
	75	508	40	C1e	3	2	163 965	2 608 606 060
	75	508	40	P0f	10	4	699 877	2 608 608 M03
	75	508	60	C1e	3	4	163 972	2 608 606 061
	75	508	80	C1e	3	4	163 989	2 608 606 062
	75	508	100	C1e	3	4	163 996	2 608 606 063
	75	508	120	C1e	3	4	164 009	2 608 606 064
	75	508	150	C1e	3	4	164 016	2 608 606 065
	75	508	180	C1e	4	4	164 023	2 608 606 066
	75	508	220	C1e	3	4	164 030	2 608 606 067
	75	533	40	C1e	3	2	164 054	2 608 606 069
	75	533	40	P0n	10	2	164 160	2 608 606 080
	75	533	40	P0f	10	2	699 914	2 608 608 M07
	75	533	60	C1e	3	4	164 061	2 608 606 070
	75	533	60	P0n	10	1	164 177	2 608 606 081
	75	533	60	P0f	10	4	699 921	2 608 608 M08
	75	533	80	C1e	3	4	164 078	2 608 606 071
	75	533	80	P0n	10	1	164 184	2 608 606 082
	75	533	80	P0f	10	4	699 938	2 608 608 M09
	75	533	100	C1e	3	4	164 085	2 608 606 072
	75	533	100	P0n	10	1	164 191	2 608 606 083
	75	533	120	C1e	3	4	247 955	2 608 607 258
	75	533	120	P0n	10	1	247 962	2 608 607 259
	75	533	120	P0f	10	4	699 945	2 608 608 M10
	75	533	150	C1e	3	4	164 092	2 608 606 073
	75	533	150	P0n	10	1	164 207	2 608 606 084
	75	533	180	C1e	3	4	247 979	2 608 607 260
	75	533	180	P0n	10	1	247 986	2 608 607 261
	75	533	220	C1e	3	4	164 108	2 608 606 074
	75	533	220	P0n	10	1	164 214	2 608 606 085
	75	610	40	C1e	3	2	164 252	2 608 606 089
	75	610	60	C1e	3	4	164 269	2 608 606 090
	75	610	80	C1e	3	4	164 276	2 608 606 091
	75	610	100	C1e	3	4	164 283	2 608 606 092
	75	610	120	C1e	3	4	164 290	2 608 606 093
	75	610	150	C1e	3	4	164 306	2 608 606 094
	100	552	40	C1e	3	2	164 979	2 608 606 161
	100	552	60	C1e	3	4	164 986	2 608 606 162


BOSCH

PRO X440 SANDING BELT

PRO

PRODUCT PROPERTIES				ORDERING INFORMATION				
Belt dimensions, width mm	Belt dimensions, length mm	Grit	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number	
100	552	80	C1e	3	4	164 993	2 608 606 163	
100	552	100	C1e	3	4	165 006	2 608 606 164	
100	552	120	C1e	3	4	165 013	2 608 606 165	
100	552	150	C1e	3	4	165 020	2 608 606 166	
100	560	40	C1e	3	2	164 498	2 608 606 113	
100	560	60	C1e	3	4	164 504	2 608 606 114	
100	560	80	C1e	3	4	164 511	2 608 606 115	
100	560	100	C1e	3	4	164 528	2 608 606 116	
100	560	120	C1e	3	4	164 535	2 608 606 117	
100	560	150	C1e	3	4	164 542	2 608 606 118	
100	610	40	C1e	3	2	164 658	2 608 606 129	
100	610	40	P0n	10	2	164 702	2 608 606 134	
100	610	60	C1e	3	4	164 665	2 608 606 130	
100	610	60	P0n	10	1	164 719	2 608 606 135	
100	610	80	C1e	3	4	164 672	2 608 606 131	
100	610	80	P0n	10	1	164 726	2 608 606 136	
100	610	100	C1e	3	4	164 689	2 608 606 132	
100	610	100	P0n	10	1	164 733	2 608 606 137	
100	610	120	C1e	3	4	247 993	2 608 607 262	
100	610	120	P0n	10	1	248 006	2 608 607 263	
100	610	150	C1e	3	4	164 696	2 608 606 133	
100	610	150	P0n	10	1	164 740	2 608 606 138	
100	620	40	C1e	3	2	164 771	2 608 606 141	
100	620	60	C1e	3	4	164 788	2 608 606 142	
100	620	80	C1e	3	4	164 795	2 608 606 143	
100	620	100	C1e	3	4	164 801	2 608 606 144	
100	620	150	C1e	3	4	164 818	2 608 606 145	
100	620	220	C1e	3	4	164 825	2 608 606 146	
100	690	40	P0f	10	2	236 164	2 608 607 199	
100	690	60	P0f	10	1	236 171	2 608 607 200	
100	690	80	P0f	10	1	236 188	2 608 607 201	
100	690	100	P0f	10	1	236 195	2 608 607 202	
100	914	40	C1e	3	2	651 455	2 608 602 345	
100	914	60	C1e	3	4	651 462	2 608 602 346	
100	914	80	C1e	3	4	651 479	2 608 602 347	
100	914	120	C1e	3	4	651 486	2 608 602 348	


BOSCH