Technical sheet


BTC40DOOR


Gateway, height 2.20 or 2.5 m, with panel

Modular warehouse barrier designed to ensure safety in industrial areas. It helps to organise vehicle traffic and demarcate high-risk zones, whilst ensuring the protection of people. Made from galvanised steel and coated with yellow epoxy paint. These various components allow for the creation of 'customized' paths:

- Available in 40 mm or 60 mm diameter tubing,
- Various post types: straight, corner, 2-sided or 3-sided,
- Various gate types: wicket gate or swing gate

Fixings available as options.







Customs code	7326909890
EAN	3321360105455

Color : Yellow

Material : Steel

Specifications :

- Gateway with access gate.
- Post diameter 40 mm.
- Fitted with 2 fixing plates 150 x 150 mm with 4 fixing holes Ø 14 mm.
- Includes a removable latch to secure the gate if required.
- Option to add (BTC40FRONT) a top panel with mounting brackets to attach a display panel.
- Do not install in environments with salt or hydrocarbons.
- Fixings optional.

Length (mm)	Width (mm)	Height (mm)	Dimensions plate (mm)	Net weight (kg)
1120	150	2150	150 x 150	19,00

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com