



Product data sheet

Power tools for trade & industry

Cordless Dust Extractor

PRO GAS18V-6LS



L-Class 18V portable dust extractor for dry applications with semi-automatic filter cleaning

The most important data

Battery voltage	18.0 V
Weight excl. battery	4 kg

Part Number 0 601 9K2 100

Technical data

Technical data

Battery voltage	18.0 V
Weight excl. battery	4 kg
Suction hose nominal width	30 mm
Filter surface area	3,000 cm ²
Max. airflow rate (turbine)	36 l/s
Max. vacuum pressure (turbine)	129 mbar
Container volume, gross	6 l
Container volume, net	4.5 l
Dust class	L
Packaging dimensions (width x length x height)	295 x 245 x 445 mm
Filter cleaning system	SFC
Anti-static hose	No
BITURBO	No
Hose variable length	0.5 - 2.8 m

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Just one 18V battery: compact L-class dry dust extractor
- Ergonomical handle and carrying strap for great portability
- Accessories (included) can be stored directly on the dust extractor for maximum convenience



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

