



 PRODUCT-DETAILS

BVBD-P366GT

COND FTNG 90DCURV PG36 NW36 IP66BLK



General Information

Extended Product Type:	BVBD-P366GT
Product ID:	7TAA292150R0104
EAN:	7630030217425
Catalog Description:	COND FTNG 90DCURV PG36 NW36 IP66BLK
Long Description:	VB Connector 90 Degree Curved Elbow, PG Thread, for IP66 Conduit - Thread PG 36, Fits to Conduit Size NW/Metric 36/40, Color Black
Display Name:	BVBD-P366GT

Additional Information

Product Main Type:	PMA Flexible Cable Protection
Application:	For Cable Protection Systems In a Wide Range of Applications
Product Type:	Fittings for Nylon Flexible Conduits

Ordering

EAN: 7630030217425

UPC: 786209948977

Technical

Number of Batteries: 0

Color: Black

Material: High-Grade Specially Formulated Polyamide/Nylon 6

Size: PG36

Environmental

WEEE Category: Product Not in WEEE Scope

Container Information

Package Level 1 Units: 20 EA

Package Level 1 EAN: 7630030217425

Package Level 1 Height: 0 mm
0 in

Package Level 1 Depth / Length: 0 mm
0 in

Package Level 1 Width: 0 mm
0 in

Certificates and Declarations

Data Sheet, Technical Information: BVBD-P366GT

Instructions and Manuals: BVBD-P366GT

Declaration of Conformity - CE: 9AKK107680A0674

External Classifications and Standards

ETIM 8: EC001176 - Screw connection for corrugated plastic hose

ETIM 9: EC001176 - Screw connection for corrugated plastic hose

UNSPSC: 39131717

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

