



## RS 4-PP10

Glass Tube Fuse, 4A, 5x20mm, Fast

### Product Properties:

Voltage type	AC/DC
Connection type	Base
Release characteristic	Fast (F)
Rated current	4 A
Rated voltage	250 V
Optical defect indication	No
Model	Glass fuse
Max. current (I <sub>max</sub> )	4 A

### Dimensions:

MOQ	10 .
Unit	pck
Rated voltage	250 V
Dimensions	5x20 mm

### Approvals:

Voltage type	AC/DC
--------------	-------

### Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Contain no Iron or Steel
REACH	No SVHC (247 Subs. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

## Other information:

<b>ETIM-Class</b>	EC002704 - Cylindrical fuse
<b>ETIM-Release</b>	9.0
<b>Trademark</b>	NECORE
<b>Product Group</b>	Glass tube fuses - Consumer pack
<b>Search Description</b>	GLASSÄKRING, 4A
<b>Alternative SKU</b>	RS4-PP10

## Logistic information:

<b>Barcode</b>	733117640873
<b>Country of origin</b>	FR
<b>Item status</b>	Non Stock Item, can be on stock but is not a regular stock item.
<b>MOQ</b>	10 .
<b>Stock code</b>	RS 4-PP10
<b>Taric code</b>	85361010
<b>Unit</b>	pck

\*We reserve the right to make technical changes and disclaim any typographical errors.