

ALPHA

8370PJD100P62

EAN 4031582490329

Swivel castor, plate fitting. stainless housing Wheel centre made of Polypropylene, Tread: TENTEpren (thermoplastic rubber), grey non-marking, roller bearing made of stainless steel



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	100 mm
Wheel width	32 mm
Size of Plate	105 x 85 mm
Plate hole centres	80/77 x 60 mm
Plate hole	9 mm
Offset	35 mm
Swivel Interference	170 mm
Overall height	128 mm
Temperature	- 20 / + 60 °C
Standard	EN_12532
Swivel Radius	85 mm
Hardness of tread	Shore A 87
Load capacity	80 kg
Load capacity (static)	160 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●