

A657 - AHR 10 Food Glove Liner - 1 glove

Collection: Cut Resistant

Range: Hand Protection

Materials: HPPE, Steel Fibre, Polyester, Nylon, Elastic

Inner Pack: 12

Outer Carton: 92

Product information

Food safe glove designed to achieve maximum Cut Level F protection. 10 gauge liner provides exceptional durability. Low linting construction prevents food contamination. Sold as a single glove. Tested for 20 washes at temperatures up to 92°C. Ambidextrous to fit right or left handed users.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (3X4XF)

ANSI/ISEA 105: 2016 CUT Level (A7)



Features

- Level F cut resistance
- Approved for safe food handling
- Machine washable up to 92°C
- Sold as a single glove
- Ambidextrous suiting left and right handed users
- Low linting construction for minimal contamination
- OEKO-TEX® STANDARD 100 approved
- Tough 10 gauge liner
- Breathable seamless liner
- CE certified
- CE foodsafe



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A657 - AHR 10 Food Glove Liner - 1 glove

Commodity Code: 6116930000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/12052-02/E01-01

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A657GRRS	Grey	42.0	30.0	35.0	0.0360	0.0441	5036108360819	15036108849595
A657GRRM	Grey	42.0	30.0	35.0	0.0480	0.0441	5036108360802	15036108849588
A657GRRL	Grey	42.0	30.0	35.0	0.0500	0.0441	5036108360796	15036108849571
A657GRRXL	Grey	42.0	30.0	35.0	0.0520	0.0441	5036108360826	15036108849601
A657GRRXXL	Grey	42.0	30.0	35.0	0.0560	0.0441	5036108360833	15036108849618