

HAP1

Item No: T0052711599N

Hot air iron 100 W, 24 V with hot air nozzle round R 06 Ø 3,0 mm



TECHNICAL DATA

Hot Air (picto)	Yes
Maximum Hot Air Flow Rate l/min (Depends on Tool)	10 l/min
Power	100 W
Supply Unit	PUWAD101 WR2 WR3M WR3ME
Temperature Accuracy °C	± 30°C
Temperature Accuracy °F	± 80°F
Temperature Range (Depends on Tool)	65 - 510°C
Temperature Range °C	50 - 550 °C
Temperature Range °F	100 - 1000 °F
Tip Type	F R D & Q Series
UPC	037103089366
Product Family	Hot Air Irons