



Polyethylene Tape

5421 • 5423

Technical Data

July, 2005

Product Description 3M™ Polyethylene Tape 5421 and 5423 has a rubber adhesive which provides an excellent abrasion resistant surface.

Product Construction	Backing	Adhesive	Liner	Color	Standard Roll Length
	Ultra-high molecular weight polyethylene	Rubber	60# densified kraft	Translucent	18 yds. (16.4 m)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
3M tape 5421		
Adhesion to Steel:	26 oz./in width (28 N/100 mm)	D-3330
Tensile Strength:	30 lbs./in. width (526 N/100 mm)	D-3759
Elongation at Break:	275%	D-3759
Backing Thickness:	5.0 mils (0.13 mm)	D-3652
Total Tape Thickness: (without liner)	6.7 mils (0.17 mm)	D-3652
Liner Thickness:	3.5 mils (0.09 mm)	D-3652
Temperature Use Range:	-30° to 225°F (-34° to 107°C)	
3M tape 5423		
Adhesion to Steel:	26 oz./in width (28 N/100 mm)	D-3330
Tensile Strength:	55 lbs./in. width (963 N/100 mm)	D-3759
Elongation at Break:	300%	D-3759
Backing Thickness:	10 mils (0.25 mm)	D-3652
Total Tape Thickness: (without liner)	11.7 mils (0.30 mm)	D-3652
Liner Thickness:	3.5 mils (0.09 mm)	D-3652
Temperature Use Range:	-30° to 225°F (-34° to 107°C)	

Features

- Thick caliper UHMW polyethylene tape for extended service life as a protective surface against extreme wear.
- UHMW polyethylene is a thermoplastic that has a unique combination of properties which make it ideal for many tough impact wear or sliding applications.
- Liner makes it ideal for fabricating or die-cutting into various lengths and shapes.
- Outstanding abrasion resistance so will outwear many types of PTFE and other materials in sliding applications.
- Low coefficient of friction exceeded only by the PTFE's.
- Self-lubricating so can often be used where lubrication is not possible because of contamination.
- Sound damping for high energy absorption capacity helps reduce noise levels in machinery and equipment.

3M™ Polyethylene Tape

5421 • 5423

Application Ideas

- Conveyor flat guide rails
- Discharge chutes
- Doctor blades
- Former noses
- Protecting aluminum sheets on stretch forming presses
- Spray booth liners
- Tank and bin liners
- Drawer and cabinet slides
- Feed and grain chutes

Storage

Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.

Product Use

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy

Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability

Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Business Industrial Adhesives and Tapes Division

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

Printed in U.S.A.
©3M 2005 70-0709-5118-4 (7/05)