



Waterproof wiring devices VDE

Mureva

Assembly surface mounted wiring devices

Switches with pre-mounted earth block



Type	Color	IP-IK	Qty per package	Ref.
------	-------	-------	-----------------	------

Conforming to EN 60669-1. Conforming to VDE 0632 Teil 1. External dimensions : 72 x 72 x 47 mm. They can be deconditioned : each product is individually packaged.

Standard

Assembly surface mounted rockers become illuminated using bulbs and indicators in option. They can carry a label using the legended push in option (see accessories page 8).

Rocker

Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35721
	White	IP 55 - IK 07	10	ENN35921

Double pole switch

Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35733
	White	IP 55 - IK 07	10	ENN35933

Changeover

Assembly surface mounted	Grey	IP 55 - IK 07	5	ENN35723
	White	IP 55 - IK 07	5	ENN35923

Illuminated

Illuminated rockers are provided with a mounted bulb.

Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35727
	White	IP 55 - IK 07	10	ENN35927

Doubles

Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35722
	White	IP 55 - IK 07	10	ENN35922

Roller shutter

Double switch interlocked for direct control. Maximum controlled power: 500 VA

Assembly surface mounted	Grey	IP 55 - IK 07	1	ENN35741
--------------------------	------	---------------	---	----------

Push-buttons with pre-mounted earth block



Conforming to EN 60669-1. Conforming to VDE 0632 Teil 1. External dimensions : 72 x 72 x 47 mm. They can be deconditioned : each product is individually packaged.

Standard

Push-buttons 10A

Les Push-buttons assembly surface mounted become illuminated using bulbs and indicators in option. They can carry a label using the legended push in option (see accessories page 8).

Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35826
--------------------------	------	---------------	----	----------

With legended

Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35730
	White	IP 55 - IK 07	10	ENN35930

With picto

Light picto Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35783
	White	IP 55 - IK 07	10	ENN35960
Bell picto Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35760

Illuminated

Push-buttons 10A illuminated

Illuminated push-buttons are provided with mounted bulbs.

Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35828
--------------------------	------	---------------	----	----------

With picto

Light picto Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35764
	White	IP 55 - IK 07	10	ENN35962
Bell picto Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35762



Switches with pre-mounted earth block (cont.)

Type	Color	IP-IK	Qty per package	Ref.
Double, can be unpacked				
Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN35832
Roller shutter				
Double push-button for an automatic control. Stop by pushing simultaneously the 2 pushes.				
Assembly surface mounted	Grey	IP 55 - IK 07	1	ENN35742



P124546

Power sockets with earth plug on side

<p>Conforming to VDE 0660. Easy cabling using box terminals. The cover opens 180°. External dimensions : 72x72x57 mm.</p>				
Standard				
Packaged by 10 units				
PC 2P+T VDE assembly surface mounted	Grey	IP 55 - IK 07	10	ENN36031
	White	IP 55 - IK 07	10	ENN39031
PC 2P+T VDE couv. transparent assembly surface mounted	Grey	IP 55 - IK 07	10	ENN36033
Can be unpacked				
PC 2P+T VDE Assembly surface mounted	Grey	IP 55 - IK 07	10	ENN36731
	White	IP 55 - IK 07	10	ENN36931
Standard Impact				
Power sockets packaged by 10 units				
PC 2P+T VDE choc en saillie	Bleu	IP 55 - IK 08	10	ENN36131



P124585



P124580

Network sockets

RJ45 sockets				
External dimensions : 72 x 72 x 57 mm.				
Cat. 5, UTP assembly surface mounted	Grey	IP 55 - IK 07	1	ENN36050
Cat. 5, FTP shielded assembly surface mounted	Grey	IP 55 - IK 07	1	ENN36051
Cat.6, FTP assembly surface mounted	Grey	IP 55 - IK 07	1	ENN36055



P124588

Signaling accessories

Signaling accessories				
<p>Signaling bulbs equipped with plugs to instal E14 type bulbs. Maximum power: 5 W à 230/250 V. Made entirely of insulating material. External dimensions : 72x72x57 mm. Provided without bulb.</p>				
Packaged by 10 units				
Clear glass assembly surface mounted	Grey	IP 55 - IK 07	10	ENN34523
Red glass assembly surface mounted	Grey	IP 55 - IK 07	10	ENN34526
Green glass assembly surface mounted	Grey	IP 55 - IK 07	10	ENN34527
Can be unpacked				
Clear glass assembly surface mounted	Grey	IP 55 - IK 07	10	ENN34723
Red glass assembly surface mounted	Grey	IP 55 - IK 07	10	ENN34726
Green glass assembly surface mounted	Grey	IP 55 - IK 07	10	ENN34727
Bulb accessory				
Bulb E14, 5W - 250V	Grey	-	10	ENN34555



P124584



P124582



P124583

Switches



Type	Color	IP-IK	Qty per package	Ref.
Conforming to EN 60669-1. Admitted to the NF-USE quality mark under the no 830 by the LCIE-UTE. External dimensions : 72 x 72 x 47 mm .				
Standard				
Packaged by 10 units				
Rocker componable surface mounted	Grey	IP 55 - IK 07	10	ENN37021
	White	IP 55 - IK 07	10	ENN39721
Can be unpacked				
Rocker componable surface mounted	Grey	IP 55 - IK 07	10	ENN37720
	White	IP 55 - IK 07	10	ENN37921
Doubles				
Packaged by 10 units				
Double rocker componable surface mounted	Grey	IP 55 - IK 07	10	ENN37022
	White	IP 55 - IK 07	10	ENN39722
Can be unpacked				
Double rocker componable surface mounted	Grey	IP 55 - IK 07	10	ENN37722
	White	IP 55 - IK 07	10	ENN37922

Push-buttons



Conforming to EN 60669-1. Admitted to the NF-USE quality mark under the no 830 by the LCIE-UTE. External dimensions : 72 x 72 x 47 mm				
Standard				
Packaged by 10 units				
Componable surface mounted	Grey	IP 55 - IK 07	10	ENN37026
	White	IP 55 - IK 07	10	ENN39726
Illuminated				
Illuminated push-buttons are provided with a mounted bulb.				
Packaged by 10 units				
Componable surface mounted	Grey	IP 55 - IK 07	10	ENN37028
	White	IP 55 - IK 07	10	ENN39728
Light picto componable surface mounted	Grey	IP 55 - IK 07	10	ENN37033
	White	IP 55 - IK 07	10	ENN39733
Bell picto componable surface mounted	Grey	IP 55 - IK 07	10	ENN37031
	White	IP 55 - IK 07	10	ENN39731
Can be unpacked				
Light picto componable surface mounted	Grey	IP 55 - IK 07	10	ENN37764
	White	IP 55 - IK 07	10	ENN37964
Bell picto componable surface mounted	Grey	IP 55 - IK 07	10	ENN37762
	White	IP 55 - IK 07	10	ENN37962

Power sockets with earth plug on side



Conforming to VDE 0660. Easy cabling using box terminals. The cover opens 180°. External dimensions : 72 x 72 x 57 mm				
Standard				
Packaged by 10 units				
PC 2P+T VDE componable surface mounted	Grey	IP 55 - IK 07	10	ENN38031
Can be unpacked				
PC 2P+T VDE componable surface mounted	Grey	IP 55 - IK 07	10	ENN38731
	White	IP 55 - IK 07	10	ENN39831

Accessories for componable and surface mounted wiring devices

P124598 - P124598 - P124602 - P124604



Type	Color	IP-IK	Qty per package	Ref.
Empty boxes surface mounted 16A with pre-mounted earth block				
Empty boxes allowing to install front plate wiring devices. Glow wire test: 650 °C - 30 s. Cable entries: ■ Simple or double empty boxes: 1 entry with E.V.A. membrane for cables and conduits + 1 flat tip ■ Triple empty boxes: 2 entries with 1 E.V.A. membrane for cables and conduits + 2 flat tips				
Empty box componable surface mounted	Grey	IP 55 - IK 07	10	ENN37711
	White	IP 55 - IK 07	10	ENN37991
Double empty box vertic. componable surface mounted	Grey	IP 55 - IK 07	5	ENN37712
	White	IP 55 - IK 07	5	ENN37992
Double empty box horiz. componable surface mounted	Grey	IP 55 - IK 07	5	ENN37714
	White	IP 55 - IK 07	5	ENN37994
Triple empty box horiz. componable surface mounted	Grey	IP 55 - IK 07	5	ENN37713
	White	IP 55 - IK 07	5	ENN37993
Frame 47 x 47				
Box 47 x47 cover opaque	Grey	IP 55 - IK 07	5	ENN35302
Box 47 x47 smoked glass	Grey	IP 55 - IK 07	5	ENN37301
Frame 45 x 45				
Inteded to install 45x45 mm mecanisms in waterproof frames. Packaged by 10 units				
Frame clear componable surface mounted	Grey	IP 55 - IK 07	10	ENN35004
Frame smoked componable surface mounted	Grey	IP 55 - IK 07	10	ENN35005
Frame opaque componable surface mounted	Grey	IP 55 - IK 07	10	ENN35006
Can be unpacked				
Empty box 45 x 45 componable surface mounted	Grey	IP 55 - IK 07	5	ENN35303
Cover frame 45 x 45 componable surface mounted	Grey	IP 55 - IK 07	5	ENN37303
Cable outlet cover				
Cable outlet cover with strain relief.				
Componable surface mounted	Grey	IP 55 - IK 07	10	ENN37731
	White	IP 55 - IK 07	10	ENN38991
E.V.A. cable entries (Easy Valve Access)				
Standard Ø 20 mm entries for conduits (Ø 16 - 20 mm) or RO2V cables Flat tips (2 x Ø 13 mm + 1 x Ø 16 mm).				
Standard Ø 20 EVA entry	Grey	-	20	ENN35008
	White	-	20	ENN39008
Flat tip	Grey	-	20	ENN35007
	White	-	20	ENN39007

P124532



P124532



Switches



P124671



P124675

Type	Color	IP-IK	Qty per package	Ref.
------	-------	-------	-----------------	------

Conforming to EN 60669-1. Admitted to the NF-USE quality mark under the no 830 by the LCIE-UTE.
External dimensions : 82 x 82 x 18,5 mm. They can be deconditioned : each product is individually packaged.

Standard

With fixing clamps

Rocker assembly flush mounted	Grey	IP 44 - IK 08	10	ENN35221
	White	IP 44 - IK 08	10	ENN34921
Changeover assembly flush mounted	Grey	IP 44 - IK 08	10	ENN35223
	White	IP 44 - IK 08	10	ENN34923

Without fixing clamps*

Rocker assembly flush mounted	Grey	IP 44 - IK 08	10	ENN34021
	White	IP 44 - IK 08	10	ENN34021
Double pole switch assembly flush mounted	White	IP 44 - IK 08	10	ENN39133
Changeover assembly flush mounted	Grey	IP 44 - IK 08	10	ENN34023

Doubles

With fixing clamps

Switch + rocker assembly flush mounted	Grey	IP 44 - IK 08	10	ENN35222
	White	IP 44 - IK 08	10	ENN34922

Without fixing clamps*

Switch + rocker assembly flush mounted	Grey	IP 44 - IK 08	10	ENN34022
--	------	---------------	----	----------

Push-buttons



P124613



P124605

Conforming to EN 60669-1. Admitted to the NF-USE quality mark under the no 830 by the LCIE-UTE.
External dimensions : 82 x 82 x 18,5 mm. They can be deconditioned : each product is individually packaged.

Standard

With fixing clamps

Assembly flush mounted	Grey	IP 44 - IK 08	10	ENN35226
	White	IP 44 - IK 08	10	ENN34926
With legended assembly flush mounted	Grey	IP 44 - IK 08	10	ENN35229
	White	IP 44 - IK 08	10	ENN34929

Without fixing clamps*

Assembly flush mounted	Grey	IP 44 - IK 08	10	ENN34026
With legended assembly flush mounted	Grey	IP 44 - IK 08	10	ENN34029

Illuminated

Illuminated push-buttons are provided with mounted bulbs.

Without fixing clamps.

Illuminated 10A P-B assembly flush mounted	Grey	IP 44 - IK 08	10	ENN34028
	White	IP 44 - IK 08	10	ENN39128

* Fixing clamps available in option page 8.

Specific switch

Roller shutter

The product is set for an automatic control. Remove the springs during assembly to change it to an interlocked double switch for a direct control.

They can be deconditioned : each product is individually packaged.

Wiring devices without fixing clamps, available in option page 8.

Assembly flush mounted	Grey	IP 55 - IK 07	1	ENN34041
	White	IP 55 - IK 07	1	ENN39141

Power sockets with earth plug on side

P124631



Type	Color	IP-IK	Qty per package	Ref.
------	-------	-------	-----------------	------

Conforming to VDE 0660.
Easy cabling using box terminals.
The cover opens 180°.
External dimensions : 82 x 82 x 22,5 mm
They can be deconditioned : each product is individually packaged.

Standard

With fixing clamps				
PS 2P+E VDE assembly flush mounted	Grey	IP 44 - IK 08	10	ENN35231
	White	IP 44 - IK 08	10	ENN34931
Without fixing clamps*				
PS 2P+E VDE assembly flush mounted	Grey	IP 44 - IK 08	10	ENN34031
	White	IP 44 - IK 08	10	ENN39131

* Fixing clamps available in option page 8.

Switches



P124622 - P124623

Type	Color	IP-IK	Qty per package	Ref.
Conforming to EN 60669-1. Admitted to the NF-USE quality mark under the no 830 by the LCIE-UTE. External dimensions : 45 x 45 mm. Wiring devices without fixing clamps, available in option page 8.				
Standard				
Rocker compo. flush mounted	Grey	IP 44 - IK 08	10	ENN34121
	White	IP 44 - IK 08	10	ENN39421
Doubles				
Double rocker compo. flush mounted	Grey	IP 44 - IK 08	10	ENN34122
	White	IP 44 - IK 08	10	ENN39422

Push-buttons



P124624 - P124625

Conforming to EN 60669-1. Admitted to the NF-USE quality mark under the no 830 by the LCIE-UTE. External dimensions : 45 x 45 mm. Wiring devices without fixing clamps, available in option page 8.				
Standard				
Compo. flush mounted	Grey	IP 44 - IK 08	10	ENN34126
	White	IP 44 - IK 08	10	ENN39426
Illuminated				
Illuminated push-buttons are provided with mounted bulbs.				
Compo. flush mounted	Grey	IP 44 - IK 08	10	ENN34128
	White	IP 44 - IK 08	10	ENN39428

Accessories for componible flush mounted wiring devices



P124653 - P124655

Double frames				
Center-to-center distance 71 mm.				
Horiz. compo. flush mounted	Grey	IP 44 - IK 08	5	ENN34101
	White	IP 44 - IK 08	5	ENN39101
Vert. compo. flush mounted	Grey	IP 44 - IK 08	5	ENN34151
	White	IP 44 - IK 08	5	ENN39151

Complementary and replacement accessories



Type	Color	IP-IK	Qty per package	Ref.
Illum. pushes + bulbs				
Changes a rocker or a push-button to an illuminated switch.				
Packaged by 10 units				
For surface mounted switches	Grey	-	10	ENN35200
	White	-	10	ENN39200
For surface mounted switches	Grey	-	10	ENN34100
	White	-	10	ENN39100
For impact switches	Bleu	-	10	ENN35100
Can be unpacked				
For surface mounted switches	Grey	-	10	ENN35800
Legended pushes (without bulb)				
Compatible with bulb ref. ENN34104.				
Packaged by 10 units				
For surface mounted switches	Grey	-	10	ENN35210
	White	-	10	ENN39210
Can be unpacked				
For surface mounted switches	Grey	-	10	ENN35810
Bulb with wires				
Replacement bulb for illuminated switches or intended to make a switch become illuminated.				
Packaged by 10 units				
Bulb 230V - 1,7 mA for surface mounted switches	Grey	-	10	ENN35300
Bulb 230V for flush mounted switches	Grey	-	10	ENN34103
Can be unpacked				
Bulb 230V for flush mounted switches	Grey	-	10	ENN35370
Bulb				
Compatible with flush mounted push-buttons (illuminated or legended).				
Bulb 230V for flush mounted switches	Grey	-	10	ENN34104
Fixing clamps				
5 sets of 2 clamps in each packaging. It can not be mounted on flush mounted time delay switches (ref. ENN34067 and ENN39167), neither on double flush mounted rockers (ref. ENN34012 et ENN34112).				
For surface mounted switches	-	-	1	ENN34102
Additional gasket for flush mounted switches.				
Assure l'IP 44 en cas d'installation sur un mur avec un état de surface grossier (crépis,...).				
For surface mounted switches	-	-	10	ENN34105
Earth block				
For surface mounted switches	-	-	10	IMT34009