

[illegible]

Packaging Specifications	
Mounting:	Bolt - M12x16
Packaging:	Bulk, Bag

Specifications	
Capacitance:	68 uF
Capacitance Tolerance:	10%
Voltage AC:	780 VAC
Voltage DC:	1700 VDC
Temperature Range:	-25/+70C
Rated Temperature:	70°C
Insulation Resistance:	10 MOhms
Max dV/dt:	70 V/us
Resistance:	1.5 mOhms (10kHz)
Ripple Current:	60 Amps (10kHz 40C)
Inductance:	170 nH

Electronic Components
KEMET
CHARGED®