



Main

Range of product	Canalis
Product or component type	Feed unit
BAR MATERIAL	Aluminium
Product compatibility	KBB
[Ie] rated operational current	25 A 40 A
Mounting location	Right
Colour	White (RAL 9003)

Complementary

Protection type	Without protection
[Ue] rated operational voltage	230...400 V
Connections - terminals	Terminal block - Pg 21 - screw clamp connector for 10 mm ²
Control type	Without
Number of circuits	1
Provided equipment	End cover
Mounting mode	By clips
Mounting support	Busbar
Standards	IEC 61439-6 IEC 60439-2
Width	244 mm
Depth	75.5 mm
Height	75.5 mm
Net weight	500 g

Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------

