

53781

Tube Brush, Ø40 mm, 510
mm, Hard, Pink



Effectively clean bottles, tubes and hard-to-reach surfaces such as gaps and crevices on machinery and conveyer belts with this handy Tube Brush.

Technical Data

Item Number	53781
Visible bristle length	17 mm
Material	Polypropylene Polyester Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	15 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	1260 Pcs.
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	530 mm
Box Width	230 mm
Box Height	150 mm
Product Diameter	40 mm
Length/Depth	510 mm
Width	40 mm
Height	40 mm
Gross Weight	0,1 kg
Net Weight	0,09 kg
Cubik metre	0,0008 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705020537813
GTIN-14 Number (Box quantity)	15705020537810
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact