

Bulkhead SSK (for gaseous medium use type SSKK)

	G mm in	h mm in	Type	Order No. (Add C6F for Standard Finish)	
				NBR (BUNA)	FPM (VITON) (Standard)
M 16	72 2.8	72 2.8	A	SSK 20-P	SSK 20-V
M 16 x 1.5¹⁾	72 2.8	72 2.8	B	SSK 20/08 S-P	SSK 20/08 S-V
M 18 x 1.5¹⁾	72 2.8	72 2.8	B	SSK 20/12 L-P	SSK 20/12 L-V
7/16 UNF (- 4 JIC)	63 2.48	63 2.48	A	N/A	SSK20-J ^{7/16} UNF-MV

¹⁾ Compression ring assembly 8 S/12 L acc. to DIN 2353

Gauge Adaptor SMA

	G mm in	h mm in	SW mm in	Order No. (Add C6F for Standard Finish)	
				NBR (BUNA)	FPM (VITON) (Standard)
G 1/4	54 2.12	54 2.12	19 .75	SMA 20 - G 1/4 - P-OR	SMA 20 - G 1/4 - V-OR
G 1/2	64 2.52	64 2.52	27 1.06	SMA 20 - G 1/2 - P-OR	SMA 20 - G 1/2 - V-OR
1/4 NPT	54 2.12	54 2.12	19 .75	SMA 20 - 1/4 NPT-P	SMA 20 - 1/4 NPT-V
1/2 NPT	64 2.52	64 2.52	27 1.06	SMA 20 - 1/2 NPT-P	SMA 20 - 1/2 NPT-V

Mounting hole Ø 18 mm (0.17")

Snubber on request

Direct Gauge Adaptor SMD

	G mm in	h mm in	SW mm in	Order No. (Add C6F for Standard Finish)	
				NBR (BUNA)	FPM (VITON) (Standard)
G 1/4	41 1.61	41 1.61	19 .75	SMD 20 - G 1/4 - P-OR	SMD 20 - G 1/4 - V-OR
G 1/2	51 2.0	51 2.0	27 1.06	SMD 20 - G 1/2 - P-OR	SMD 20 - G 1/2 - V-OR
1/4 NPT	41 1.61	41 1.61	19 .75	SMD 20 - 1/4 NPT	SMD 20 - 1/4 NPT
1/2 NPT	51 2.0	51 2.0	27 1.06	SMD 20 - 1/2 NPT	SMD 20 - 1/2 NPT
7/16 - 20 UNF	41 1.61	41 1.61	19 .75	—	SMD 20 - 7/16 UNF

Snubber on request

Swivel Run Tees SGV

	Order Code Without Test Point								
	Thread G	Ød1 mm in	Ød2 mm in	I1 mm in	I2 mm in	I3 mm in	I4 mm in	Hex1 mm in	Hex2 mm in
7/16 - 20 UNF	7.49 .29	4.9 .19	9 .35	14 .55	37 1.46	8 .31	27 1.06	17 .67	SGV 7/16 UNF - 04 - JIC 1/4 - F/M
9/16 - 18 UNF	11.1 .44	8.1 .32	10.5 .41	14.1 .56	37.6 1.48	8.5 .33	27 1.06	19 .75	SGV 7/16 UNF - 06 - JIC 3/8 - F/M
3/4 - 16 UNF	14.5 .57	10.8 .43	10.5 .41	16.7 .66	48.7 1.92	8.5 .33	27 1.06	22 .87	SGV 7/16 UNF - 08 - JIC 1/2 - F/M
1-1/16 - 12 UNF	21.0 .83	15.5 .61	14 .55	21.9 .86	51.5 2.03	13.5 .53	31.5 1.24	31.5 1.24	SGV 7/16 UNF - 12 - JIC 3/4 - F/M
1.5/16 - 12 UNF	27.5 1.08	21.3 .84	15.3 .60	23.3 .92	57.0 2.24	14.8 .58	38 1.50	38 1.50	SGV 7/16 UNF - 16 - JIC 1 - F/M
Order Code Including Test Point									
including SMK 20-7/16 UNF-VE - C6F					including SKK20-7/16 UNF-VE - C6F				
SMK 20 - 04- JIC 1/4 - F/M-1137					SKK 20 - 04- JIC 1/4 - F/M-1137				
SMK 20 - 06- JIC 3/8 - F/M-1137					SKK 20 - 06- JIC 3/8 - F/M-1137				
SMK 20 - 08- JIC 1/2 - F/M-1137					SKK 20 - 08- JIC 1/2 - F/M-1137				

Other threads available on request.