



120-240V, 150WATTS CS060, 06020.0-00,

Model		
product brand name	SIVACON	
product designation	heater unit	
design of the product	Semiconductor	
General technical data		
consumed active power rated value	150 W	
Voltage		
type of voltage of the operating voltage	AC/DC	
continuous heating power at 20 °C	150 W	
operating voltage		
• rated value minimum	120 V	
• rated value maximum	240 V	
• at AC at 50 Hz rated value minimum	120 V	
• at AC at 50 Hz rated value maximum	240 V	
• at AC at 60 Hz rated value minimum	120 V	
• at AC at 60 Hz rated value maximum	240 V	
• at DC rated value minimum	120 V	
• at DC rated value maximum	240 V	
Protection class		
protection class IP	IP20	
Product details		
product component		
• blower	No	
• thermostat	No	
Mechanical Design		
height	150 mm	
width	60 mm	
depth	90 mm	
Approvals Certificates		
General Product Approval	other	Environment



EG-Konf.



UR



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2131-5A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2131-5A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2131-5A

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

