

OGL24II-1



Sample image

Order symbol : OGL24II-1

Product nr : 2550362

Description : Cover with hinged inspection window

EAN : 6418074301543

El. number :

- Finland : 3424810
- Denmark : 8212007521
- Sweden : 2507772

Dimensions :	Height	Width	Depth
mm :	280	280	55
inch :	11.02	11.02	2.17

Materials :

Material :	Polycarbonate
Gasket material :	Polyurethane

Ratings :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Not insulated
UV resistance :	-
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175