

Video Combination Cable 50 m

Art. no. KA9002

Page 1 of 1



- Combined cable for video and power supply
- Coaxial cable with 75 Ohm impedance
- Power line 2x 0.75 mm²

Use the video combination cable to connect individual components and ensure high-quality data transmission. The two integrated power wires (2x 0.75mm²) supply connected equipment with electricity. The cable impedance is 75 Ohm. The video combination cable is available in three lengths: 50 m (KA9002), 100 m (KA9001) and 250 m (KA9000).

Technical Data:

Cores	RG59, 2x 0,75mm ²
Application purpose	indoors
Outer diameter	9.8 mm
Diameter	9.8 mm
Housing material	PVC
Insulation	1,0

Cable type	Combined video cable
Cable length	50 m
Max. operating temperature	70 °C
Min. operating temperature	-10 °C
AC voltage supply	24 V
DC voltage supply	12 V