



## ANSMANN Home Socket HS220

Compact 20 W socket adapter with additional USB-A & USB-C socket.

### Features

- versatile socket adapter
- 250 V socket
- Integrated USB ports (USB-A and USB-C) with 20 W output
- Space-saving design
- Use at home, in the office or when travelling
- Robust construction and high-quality materials
- Long battery life



Article number: 1001-0184

Product content: Socket adapter, operating instructions



### Specifications

<b>Output voltage</b>	5V DC			
<b>Input voltage</b>	100 - 240V AC			
<b>Max. output current</b>	3 A			
<b>Charging currents</b>	<b>Mode</b>	<b>Voltage range</b>	<b>Max. current</b>	<b>Max. power</b>
	USB A	5 V	3,0 A	15,0 W
	USB A	9 V	2,0 A	18,0 W
	USB A	12 V	1,5 A	18,0 W
	USB C	5 V	3,0 A	15,0 W
	USB C	9 V	2,2 A	20,0 W
	USB C	12 V	1,7 A	20,0 W
	PPS	3,3 - 5,9 V	3,0 A	17,7 W
	PPS 2	5 - 11 V	1,8 A	19,8 W
	USB A + USB C	5 V	3,0 A	15,0 W
	Steckdose	230 V AC	16,0 A	3680,0 W
<b>USB-Ports</b>	2			
<b>Port</b>	USB-A / USB type C			
<b>Maximum power</b>	20 W			
<b>Average operational efficiency</b>	82,7 %			
<b>Efficiency at low load</b>	82,2 %			
<b>Power consumption at no load</b>	0,100 W			
<b>Charging protocol</b>	Power Delivery Profile 3 / Power Delivery Profile 2 / PPS / Quick Charge 2.0 / Quick Charge 3.0 / Quick Charge 4.0			

<b>Color</b>	white
<b>Operating temperature</b>	0 - 25 °C
<b>Storage temperature</b>	-40 - 80 °C
<b>Dimensions</b>	0 × 0 × 0 mm